



2 Type
T With draw axle
TF With draw hook



Size	F _H in N Holding capacity	a ₁	a ₂	b ₁	b ₂	b ₃	d ₁	d ₂	d ₃	h ₁ ≈	h ₂
200	2000	37	29	35	45	18	10	8	6,5	49	16
300	3000	35	25	48	60	21	10	10	8,5	49	18
400	4000	43	30	54	84	26	14	12	10,5	60,5	25

Size	l ₁ ≈	l ₂ ≈	l ₃ ≈	m ₁	m ₂	m ₃	r ₁ ≈	r ₂	s	W ₁ Stroke	W ₂ ≈ Adjustable range
200	202	51	93	32	8	19	102	5	3	100	20
300	225	51	98	45	8	32	105	6	3	104	20
400	278	58	117,5	60	12,5	28,5	138	7	5	160	20

Specification

- Sheet metal parts
Case-hardened steel C10
Zinc plated, blue passivated
- Draw hook
Steel St 37
Zinc plated, blue passivated
- All moving parts
Lubricated with special grease
- Solid designed plastic handle
Red, oil resistant
- RoHS

Information

The draw hook of the latch type toggle clamps GN 850 can be adjusted within the stroke.

see also...

- [General Information to Toggle Clamps](#) → Page 698

How to order

GN 850-300-TF

1 Size

2 Type

