



- 2 Type**
- A** Connector straight
 - B** Connector 45°
 - C** Connector 90°

Size	d ₁ Connection thread for GN 880	Length I			d ₂ Hose liner	d ₃ Nominal width Hose	d ₄ ≈
		Hose length					
22	M 22 x 1,5	250	500	1000	15	14	15,5
26	M 26 x 1,5	250	500	1000	20	19	20

Specification

Connecting nut with hose liner
Brass

L bend 45° / 90°
Copper

O-ring
Acrylonitrile butadiene rubber (NBR)

Drain hose
Polyvinyl chloride (PVC)
transparent **T**

Hose clip for type B / C
Steel, zinc plated

Plug
Plastic, Polyethylene (PE-LD)
RoHS

On request

- Other hose lengths
- Drain hose with inside webbing (Nylon)

Connector pieces GN 880.1 are required when using oil drain valves GN 880. Screwing on the connector piece will activate the valve plate of the oil drain valve, allowing the oil to flow through the hose into a pan held ready. The plug prevents remaining oil from dripping out after discharging.

see also... **Page**
GN 880 Oil Drain Valves QVX

Technical Information
 Plastic Characteristics QVX

How to order (without drain hose)	1 Size
	2 Type

GN 880.1-26-C

How to order (with drain hose)	1 Size
	2 Type
	3 Length of the hose
	4 Specification of the hose

GN 880.1-22-A-500-T