



ROSTFREI
Inox
Stainless
Steel

1

2

3

d ₁	b	l ₁	d ₂	l ₃	Size	GN 851 / GN 851.3		GN 851.1 / GN 851.2		
						r at w ₂ = 0	w ₂	Size	r at w ₂ = 0	w ₂
M 4	21	56*	3,4	27,5	160	35	11	-	-	-
M 4	21	70**	3,4	28,5	160	48	12	160	52	10
M 4	21	103	3,4	30	160	80	14	160	82	14
M 4	21	153	3,4	35	160	125	19	160	127	19
M 4	21	203	3,4	35	160	175	19	160	177	19
M 6	32	78*	5,2	33	320	54	13	-	-	-
M 6	32	110**	5,2	44	320	75	24	320	78	21
M 6	32	130	5,2	45	320	94	25	320	94	25
M 6	32	155	5,2	45	320	119	25	320	119	25
M 6	32	205	5,2	45	320	169	25	320	169	25
M 8	38	111*	7,2	52	700	70	26	-	-	-
M 8	38	127	7,2	60	700	78	34	-	-	-
M 8	38	143**	7,2	56	700	102	30	700	102	25
M 8	38	157	7,2	60	700	108	34	700	108	34
M 8	38	207	7,2	60	700	158	34	700	158	34

* These square U-bolt lengths are included in the delivery of standard orders for GN 851 / GN 851.3.
 ** These square U-bolt lengths are included in the delivery of standard orders for GN 851.1 / GN 851.2.

Specification

- Steel **ST**
- Zinc plated, blue passivated
- Stainless steel AISI 304 **NI**
- Hex nuts (with polyamide insert)
 M4: DIN 934 / DIN 985
 M6 / M8: DIN 936 / DIN 985
 - Steel, zinc plated (for ST)
 - Stainless steel (for NI)
- *Stainless Steel Characteristics* → Page 2166

• RoHS

On request

- Stainless steel AISI 316 **A4**

Information

see also...

- *Latch Type Toggle Clamps GN 851* → Page 756
- *Latch Type Toggle Clamps GN 851.1* → Page 760
- *Latch Type Toggle Clamps GN 851.2* → Page 762
- *Latch Type Toggle Clamps GN 851.3* → Page 758

How to order

1	d ₁
2	b
3	l ₁
4	Material

GN 951.1-M6-32-130-NI