



1.1

1.2

1.3

1.4

1

2

d ₁			d ₂	d ₃	h ₁	h ₂ ≈	Length l ≈
GN 99.7	GN 99.8 AISI 304	GN 99.8 AISI 316L (A4)					
16	16	16	M 8	10	12,5	26	47,5
20	20	20	M 10	12	15	32	59,5
25	25	25	M 12	14	19	40	75,5
32	32	-	M 16	18	25	52	94,5
40	40	-	M 20	20	31	62	118

2.1

Specification

3

- GN 99.7**
Steel —
Zinc plated, blue passivated
- GN 99.8**
Stainless steel —
- AISI 304 —
- AISI 316L **A4**
- Matte shot-blasted
- Shaft butt-welded
- Stainless Steel Characteristics → Page 2166
- RoHS

Information

see also...

- Clamp Nuts GN 206.1 (Cast Iron) → Page 509
- Stainless Steel Clamp Nuts GN 206.1 → Page 509

2.2

2.3

How to order (Steel)	1	d ₁
GN 99.7-20-M10	2	d ₂

2.4

How to order (Stainless steel, AISI 304)	1	d ₁
GN 99.8-32-M16	2	d ₂

How to order (Stainless steel, AISI 316L)	1	d ₁
GN 99.8-25-M12-A4	2	d ₂
	3	Material

