

Standard parts in this product family are compatible with aluminum profiles from the i and b modular systems (Page 1744), as well as with common aluminum profile systems from other manufacturers. Using slot nuts (Page 1748 / 1776) or hammerhead screws (Page 1779) or nuts (Page 1778), Ganter standard elements can be easily and cost-effectively mounted in the groove of the profiles.

- for groove widths 6, 8 and 10 mm
- for grid size 30, 40 and 45 mm



GN 565.1
Cabinet U-Handles
Aluminum,
Mounting from
the operator's side
[Page 89](#)



GN 565.2
Inclined
Cabinet U-Handles
Aluminum
[Page 88](#)



GN 630.1
Cabinet U-Handles
Plastic
ganternorm.com



GN 528
Cabinet U-Handles
Plastic
[Page 100](#)



GN 728
Cabinet U-Handles
Aluminum
[Page 104](#)



GN 728.5
Cabinet U-Handles
Stainless steel
[Page 104](#)



GN 628
Cabinet U-Handles
Plastic
[Page 113](#)



GN 629
Cabinet U-Handles
Plastic,
with cover cap
[Page 122](#)



GN 629.1
Cabinet U-Handles
Plastic
[Page 122](#)



GN 181
Fastening Sets
Zinc die casting,
for mounting
cabinet U-handles
[Page 140](#)



GN 328
Cabinet U-Handles
Aluminum
[Page 142](#)



GN 328.5
Cabinet U-Handles
Stainless steel
precision casting
[Page 142](#)



GN 333.1
Tube Handles
Tube aluminum,
legs zinc die casting
[Page 158](#)



GN 333
Tube Handles
Tube aluminum,
legs zinc die casting
[Page 164](#)



GN 667
Cabinet U-Handles
Aluminum,
end pieces plastic
[Page 166](#)



GN 667
Cabinet U-Handles
Stainless steel,
end pieces plastic
[Page 166](#)





GN 334.1
Oval Tubular Handles
Tube aluminum,
Legs zinc die casting
[Page 168](#)



GN 335
Oval Tubular Handles
Tube aluminum,
Legs zinc die casting
[ganternorm.com](#)



GN 630
Ledge Handles
Plastic
[ganternorm.com](#)



GN 412
Indexing Plungers
Zinc die casting,
with flange for mounting,
with / without rest position
[Page 884](#)



GN 416
Spring Latch
Guide zinc die casting,
plunger pin steel,
with flange for mounting
[Page 885](#)



GN 416.1
Locators
for spring latch GN 416,
zinc die casting
[Page 886](#)



GN 417.1
Locators
for indexing plungers GN 417,
steel / stainless steel
precision casting
[Page 887](#)



GN 417
Indexing Plungers
Zinc die casting,
with lifting ring / wire loop,
without rest position
[Page 888](#)



GN 417
Indexing Plungers
Stainless steel
precision casting,
with lifting ring / wire loop,
without rest position
[Page 888](#)



GN 417
Indexing Plungers
Steel,
with knob,
with / without
rest position
[Page 889](#)



GN 417
Indexing Plungers
Stainless steel,
with knob,
with / without
rest position
[Page 889](#)



GN 722.6
Indexing Plungers
Steel,
with flange for mounting,
without rest position
[Page 890](#)



GN 722.6
Indexing Plungers
Stainless steel,
with flange for mounting,
without rest position
[Page 890](#)



GN 722.6
Indexing Plungers
Steel,
with flange for mounting,
with rest position
[Page 891](#)



GN 722.6
Indexing Plungers
Stainless steel,
with flange for mounting,
with rest position
[Page 891](#)



GN 722.6
Indexing Plungers
Steel,
with flange for mounting,
with rest position, with latch
[Page 892](#)



GN 722.6
Indexing Plungers
Stainless steel,
with flange for mounting,
with rest position, with latch
[Page 892](#)



GN 724.6
Indexing Plungers
Steel / stainless steel,
with chamfered pin,
with flange for mounting
[Page 894](#)



GN 412.1
Mounting blocks
Zinc die casting,
for indexing plungers /
cam action
indexing plungers
[Page 914](#)



GN 612.2
Cam Action
Indexing Plungers
Steel,
with flange for mounting
[Page 926](#)



GN 612.9
Cam Action
Indexing Plungers
Zinc die casting,
with flange for mounting
[Page 927](#)



GN 722.3
Spring Latches
Steel,
with flange for mounting
[Page 928](#)



GN 722.3
Spring Latches
Stainless steel,
with flange for mounting
[Page 928](#)



GN 724.3
Spring Latches
Steel / stainless steel,
with chamfered pin,
with flange for mounting
[Page 930](#)



GN 3492
Mounting Blocks
Stainless steel
[Page 973](#)



GN 1050
Quick Release
Couplings
Housing aluminum
[Page 1118](#)



GN 1050.1
Studs
for quick release couplings
GN 1050,
Steel
[Page 1120](#)



GN 1050.2
Flanges
for quick release couplings
GN 1050,
Steel
[Page 1121](#)



GN 449.1
Spring-Bolt
Door Latches
Plastic,
adjustable,
with / without finger handle
[ganternorm.com](#)



GN 449.4
Snap Latches
Plastic,
with gripping tray
[Page 1248](#)



GN 936
Slam Latches
Zinc die casting,
mit / ohne Schloss
[Page 1250](#)



GN 4490
Ball Catches
Zinc die casting
[Page 1252](#)



GN 4490
Ball Catches
Stainless steel
[Page 1252](#)



GN 4490.1
Montagebleche
Stainless steel,
für GN 4490
[ganternorm.com](#)



GN 4490.2
Montagebleche
Stainless steel,
für GN 4490
[ganternorm.com](#)



GN 702
Sperrriegel
Zinc die casting,
mit / ohne Führungssteg
[Page 1256](#)



GN 938
Hinges
Zinc die casting,
für Flächenelemente
[Page 1304](#)



GN 2295
Hinges
Aluminum,
dreiteilig
[Page 1322](#)



GN 2295
Hinges
Aluminum,
dreiteilig,
vertikal verlängert
[Page 1323](#)



GN 2291
Hinge leafs
Aluminum,
mit / ohne Führungssteg
[ganternorm.com](#)





**GN 159
Hinges**
Plastic
Page 1324



**GN 159.1
Doppel-Hinges**
Plastic
ganternorm.com



**GN 161
Hinges**
Zinc die casting
ganternorm.com



**GN 127
Hinges**
Zinc die casting,
adjustable
Page 1368



**GN 127
Hinges**
Stainless steel,
adjustable
Page 1368



**GN 236
Hinges**
Plastic,
adjustable
Page 1369



**GN 151.4
Hinges**
Plastic,
adjustable
durch Langlöcher
ganternorm.com



**GN 2292
Hinges**
Aluminum,
mit Führungssteg,
aushängbar
ganternorm.com



**GN 2294
Hinges**
Aluminum,
aushängbar
ganternorm.com



**GN 139.1
Hinges
with Safety Switch**
Zinc die casting
Page 1390



**GN 139.2
Hinges**
Zinc die casting,
without switch
Page 1390



**GN 139.3
Mounting Plates**
Steel,
for hinges
GN 139.1 / GN 139.2
ganternorm.com



**GN 139.4
Mounting Plates**
Zinc die casting,
for hinges
GN 139.1 / GN 139.2
ganternorm.com



**GN 239.6
Hinges
with Safety Switch**
Plastic
Page 1394



**GN 239.7
Hinges**
Plastic,
without switch
Page 1394



**GN 239.8
Mounting Plates**
Plastic,
for hinges
GN 239.6 / GN 239.7
ganternorm.com



**GN 239.4
Hinges
with Switch**
Plastic
Page 1396




**GN 239.3
Hinges**
Plastic,
without switch
Page 1396



**GN 145
Flanged
Connector Clamps**
Aluminum
Page 1814



**GN 145
Flanged
Connector Clamps**
Stainless steel
Page 1814



GN 146.3
Flanged
Connector Clamps
Aluminum
Page 1815



GN 146.9
Flanged
Connector Clamps
Plastic
Page 1817



GN 162.3
Base Plate
Connector Clamps
Aluminum /
stainless steel
Page 1820



GN 231
Tube Supports
Aluminum
Page 1830



GN 271
Swivel Clamp
Connector Bases
Aluminum
Page 1834



GN 271
Swivel Clamp
Connector Bases
Stainless steel
Page 1834



GN 281
Swivel Clamp
Connector Joints
Aluminum /
stainless steel
Page 1838



GN 271.4
Sensorhalter
Aluminum
ganternorm.com



GN 473
Base Plate
Mounting Clamps
Aluminum
Page 1860




GN 175
Base Plate
Mounting Clamps
Plastic
Page 1861



GN 477
Mounting Clamps
Aluminum
Page 1862



GN 480
Flanged Mounting Bolts
Steel
Page 1876



GN 485
Fuß-Laschen-
Klemmhalter
Aluminum
Page 1877



GN 967
Angle Pieces,
Shackles
Steelblech,
for profile systems
Page 1886



GN 3490
Threaded Flanges
Steel Precision Casting,
for profile systems
Page 1887



GN 939
Panel
Support Clamps
Zinc die casting
Page 1888



GN 938.1
T-Nuts
Zinc die casting,
for GN 938 / GN 939
Page 1891



GN 649
Panel
Support Clamps
Plastic
Page 1892



GN 4470
Magnetic Catches
mit gummierter Haftfläche
Page 2244



GN 56
Retaining Magnets
Housing plastic
ganternorm.com

