

1 b	2 Length l ±0,25	a	h	r
12	55*	8	40	8
12	88*	8	40	8
12	100	8	40	8
12	120*	8	40	8
12	180*	8	40	8
12	200	8	40	8
12	235*	8	40	8

* suitable for 19“ rack and enclosure layout

Specification

3

GN 427
Aluminum
- Powder coated
  - Black, RAL 9005, textured finish ● **SW**
  - Silver, RAL 9006, textured finish ● **SR**
- Anodized, natural color ● **EL**

GN 427.5
Stainless steel AISI 304
Matte shot-blasted

RoHS

Cabinet U-handles GN 427 / GN 427.5 are produced from profiled aluminum extrusions.

see also...	Page
GN 425 Cabinet U-Handles (Aluminum / Stainless Steel)	QVX

echnical Information	
Load Rating Information	QVX
Stainless Steel Characteristics	QVX

How to order (Aluminum)		
1 2 3	1	b
GN 427-12-120-EL	2	Length l
	3	Finish

How to order (Stainless steel)		
1 2	1	b
GN 427.5-12-180	2	Length l