



ELESA Original design PW12

3 Type

- R** Numbers ascending clockwise
L Numbers ascending anti-clockwise

1

2

d ₁	Counter	indication after 1 spindle revolution	corresponds to thread pitch	Scale		d ₂	d ₃	l ₁	l ₂
				Number of graduations	Indication precision of the pointer				
60	0000.2	000002	0,2	20	0,01	68,5	67	33	26
60	0000.5	000005	0,5	50	0,01	68,5	67	33	26
60	0001.0	000100	1,0	100	0,01	68,5	67	33	26
60	0002.0	000200	2,0	40	0,05	68,5	67	33	26
60	0002.5	000250	2,5	50	0,05	68,5	67	33	26
60	0003.0	000300	3,0	60	0,05	68,5	67	33	26
60	0004.0	000400	4,0	80	0,05	68,5	67	33	26
60	0005.0	000500	5,0	100	0,05	68,5	67	33	26

Specification

- Housing
Plastic (Polyamide PA)
- glass fiber reinforced
- black, matte
 - Sight glass
Plastic (Polyamide PA)
- clear glass, ageing proof
- shock-resistant
 - Housing / Sight glass
- temperature resistant up to 100 °C
- oil and solvent proof
(not suitable for alcohol)
 - Pointer plastic, red
 - Scale aluminum
- matte anodized
- graduations black
 - Counter numbers white
Number wheels for integers black
for decimals red
 - Protection class IP 65
 - *Plastic characteristics* → Page 1483
 - **RoHS**
- On request**
- Special scales

Information

Position indicators GN 000.13 have been shaped for installation into different operating elements.

The salient features of these counters are:

The housing, the hand spindle, and safety glass are produced from **one single piece** of material and ultrasonically welded to give a spray water proof and corrosion free unit (Protection class IP 65).

The installation principle with the forced drive allows the use of the positioning indicator GN 000.13 in any position even in case of strong vibration.

One complete revolution of the red pointer corresponds to one revolution of the spindle. This gives a very accurate reading and, combined with the digital indication from the counter, it is very simple to read.

see also...

- *More information to position indicators GN 000.13* → Page 289
- *Disk handwheels GN 323.9 for GN 000.13* → Page 292
- *IP-Protection classes* → Page 1482

How to order

1	d ₁
2	Counter
3	Type

GN 000.13-60-0001.0-R