



4 Form
A rundstirnig

1 b h9	2 h	3 Länge l														für Wellen-Ø über bis
		6	8	10	12	14	16	18	20	-	-	-	-	-	-	
3	3	6	8	10	12	14	16	18	20	-	-	-	-	-	-	8...10
4	4	10	12	14	16	18	20	22	25	28	32	-	-	-	-	10...12
5	5	10	12	14	16	18	20	22	25	28	32	36	40	45	50	12...17
6	6	14	16	18	20	22	25	28	32	36	40	45	50	56	63	17...22
8	7	16	18	20	22	24	25	28	32	36	40	45	50	56	63	22...30
10	8	20	22	25	28	32	36	40	45	50	56	63	70	80	90	30...38
12	8	25	28	32	36	40	45	50	56	63	70	80	90	100	-	38...44

Ausführung	5
Edelstahl 1.4571	NI
RoHS	
Auf Anfrage	
• b = 14, 16, 18, 20	

Passfedern DIN 6885 sind nur in Verpackungseinheiten von 10 Stück je Größe und Länge lieferbar.

Hinweise	Seite
DIN 6885 Passfedern (Stahl)	1112

Technische Informationen	
Passfedernuten DIN 6885-1 (hohe Nabennut)	2386
Passfedernuten DIN 6885-2 (niedrige Nabennut)	2387
ISO-Passungen	2391
Edelstahl-Eigenschaften	2422

Bestellbeispiel	1 b
	2 h
	3 Länge l
	4 Form
	5 Werkstoff
DIN 6885-10-8-36-A-NI	