



### 3 Type

F With fixed handle

1

2

No.	d <sub>1</sub> H7 Bore	d <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub>	d <sub>5</sub>	h <sub>1</sub>	h <sub>2</sub> ≈	Length l
100	B 7	13	16	18	10	13	31	25
101	B 8	15	19	20	13	17	40	28
102	B 8	16	20	22	14	17	45	34
103	B 10	18	23	25	16	19,5	50	41
104	B 12	20	26	28	18	21,5	56	50

## Specification

### Body

Steel

- Turned
- Zinc plated, blue passivated

### Fixed Handle DIN 39

Steel

Zinc plated, blue passivated

RoHS

Tri-ball handles GN 10 allow fine adjustment.

An alternative in modern design are cranked handles GN 510 and control handles GN 112.1.

see also...

**GN 510** Cranked Handles (Plastic) Page QVX

**GN 112.1** Control Handles (Zinc die casting) Page QVX

### Technical Information

ISO Fundamental Tolerances

QVX

How to order

**GN 10-104-B12-F**

1 No.

2 d<sub>1</sub>

3 Type