



ELESA Original design GW12

**3 Type**

- R** Numbers ascending clockwise
- L** Numbers ascending anti-clockwise

**1**

**2**

d <sub>1</sub>	Counter	indication after 1 spindle revolution	Scale		d <sub>2</sub>	d <sub>3</sub>	l <sub>1</sub>	l <sub>2</sub>
			Number of graduations	Indication precision of the pointer				
60	0000.2	00002	20	0,01	68,5	67	33	26
60	0000.5	00005	50	0,01	68,5	67	33	26
60	0001.0	00010	100	0,01	68,5	67	33	26
60	0002.0	00020	40	0,05	68,5	67	33	26
60	0002.5	00025	50	0,05	68,5	67	33	26
60	0003.0	00030	60	0,05	68,5	67	33	26
60	0004.0	00040	80	0,05	68,5	67	33	26
60	0005.0	00050	100	0,05	68,5	67	33	26

**Specification**

- Housing Plastic (Polyamide PA)
  - glass fiber reinforced
  - black, matte
- Sight glass plastic (Polyamide PA)
  - clear glass, ageing proof
  - shock-resistant
- Housing / Sight glass
  - temperature resistant up to 100 °C
  - oil and solvent proof (not suitable for alcohol)
- Pointer plastic, red
- Scale aluminum
  - matte anodized
  - Graduation lines black
- Counter
  - Numbers white
  - Number wheels for integers black, decimals red
- Pendulum system on ball bearings
- Protection class IP 67
- RoHS

**On request**

- Special scales

**Information**

Position indicators GN 000.3 have been shaped for installation into different operating elements.

The salient features of these counters are:

The housing, the hand spindle, and safety glass are produced from **one piece** of material and ultrasonically welded to give a spray water proof and corrosion free unit (Protection class IP 67).

The pendulum system is fitted with ball bearings to give the most accurate reading usable up to a spindle inclination of 60° angular.

The numbers in the counter are very clear and the decimal numbers are shown in red.

One complete revolution of the red pointer corresponds to one revolution of the spindle. This gives a very accurate reading and, combined with the digital indication from the counter, it is very simple to read.

see also...

- *More information to position indicators GN 000.3*
- *Hand knobs, hand wheels with GN 000.3*
- *IP Protection classes → Page 1482*

**How to order**

**GN 000.3-60-0001.0-R**

- 1** d<sub>1</sub>
- 2** Counter
- 3** Type