



1.1  
1.2  
1.3  
1.4

1

2

d <sub>1</sub>	d <sub>2</sub>		d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub> ≈	h <sub>4</sub> Stroke	l <sub>2</sub>	t min.
14	M 5	M 6	10	25	4,5	35	3,5	45	9
18	M 6	M 8	13,5	31	6,5	45	4	62	11
22	M 8	M 10	16	36	8	52	4	74	14
25	M 10	M 12	19	43	11	63	4	89	17
30	M 12	M 16	23	50,5	12	76	5	108	22

2.1

Specification

3

- Handle  
Zinc die casting
- Plastic coated  
black, RAL 9005, textured finish ● SW  
orange, RAL 2004, textured finish ● OS
- Threaded bushing and retaining screw  
Stainless Steel AISI 303
- Stainless Steel characteristics → Page 1489
- RoHS

Information

Adjustable hand levers GN 101 are ideal whenever parts have to be clamped in a confined space or in a particular lever position. The centre insert is connected to the lever via serrations which can easily be disengaged.

Pulling the lever disengages serrations and allowing to be swivelled to the ideal clamping position. On releasing the lever the serrations automatically re-engage.

see also...

- Adjustable hand levers GN 101 (bushing Steel) → Page XYZ
- Adjustable hand levers GN 300.1 (bushing Stainless Steel) → Page 322
- Adjustable hand levers GN 300.2 (bushing steel, zinc plated) → Page XYZ
- Flat adjustable hand levers GN 302.1 (bushing Stainless Steel) → Page XYZ
- Adjustable Stainless Steel-Hand levers GN 300.5 → Page 324
- Adjustable hand levers GN 604.1 (Handle plastic) → Page 340

2.2  
2.3  
2.4

How to order

GN 101.1-25-M12-OS

- 1 d<sub>1</sub>
- 2 d<sub>2</sub>
- 3 Color

