




1			2			3														
d ₁	d ₂			l ₁						d ₃	h ₁	h ₂	h ₃	h ₄ Stroke	l ₂					
14	M 5	M 6		12	16	20	25	32	40	50	10	25	4,5	35	3,5	45				
18	M 6	M 8		16	20	25	32	40	50	63	13,5	31	6,5	45	4	62				
22	M 10	-		20	25	32	40	50	63	80	16	36	8	52	4	74				
25	M 12	-		25	32	40	50	63	80	-	19	43	11	63	4	89				
30	M 16	-		32	40	50	63	80	-	-	23	50,5	12	76	5	108				

Specification

Handle

- Zinc die casting
- Powder coated
- Black, RAL 9005, textured finish
- Orange, RAL 2004, textured finish

- SW
- OS

Insert / Retaining screw

- Steel
- Property class 5.8
- Blackened

RoHS

Adjustable hand levers GN 101 are ideal whenever parts have to be clamped in a confined space or in a particular lever position. The centre insert is connected to the lever via serrations which can easily be disengaged. Pulling the lever disengages serrations and allowing to be swivelled to the ideal clamping position. On releasing the lever the serrations automatically re-engage.

see also...	Page
GN 101.1 Adjustable Hand Levers (Insert Stainless Steel)	QVX
GN 300 Adjustable Hand Levers (Insert Steel, Blackened)	QVX
GN 302 Flat Adjustable Hand Levers (Insert Steel, Blackened)	QVX
GN 300.2 Adjustable Hand Levers (Insert Steel, Zinc Plated)	QVX
GN 602.1 Adjustable Hand Levers (Insert Stainless Steel)	QVX
GN 503 Adjustable Hand Levers (Handle Plastic)	QVX

Technical Information

Strength Values of Screws	QVX
---------------------------	-----

How to order	1 d ₁
	2 d ₂
	3 l ₁
	4 Color
GN 101-22-M10-40-SW	