



d ₁	d ₂	Static load in N ≈	Suitable for ball lock pins and locking pins with pin Ø										
			GN 113.1 GN 113.3 GN 113.4 GN 113.7 GN 113.8 GN 113.9 GN 113.10	GN 113.5 GN 113.6	GN 113.11 GN 113.12	GN 114.2 GN 114.3 GN 114.6 GN 114.7 GN 114.8	GN 114.11 GN 114.12	GN 124.1 GN 124.2 GN 124.3	GN 214.2 GN 214.3 GN 214.6	GN 314			
14	1	50	5 / 6 / 8	all	5 / 6 / 8 / 10	all	6 / 8	6 / 8 / 10 / 12	all	8 / 10	6 / 8	-	
18	1,3	90	10 / 12 / 16 / 20 / 25	-	12 / 16	-	10 / 12 / 16 / 20	16 / 20	-	10 / 12	10 / 12 / 16 / 20 / 25	8 / 10 / 12	
24	1,5	100	-	-	20 / 25	-	-	-	-	-	-	16 / 20	
30	1,8	120	-	-	-	-	-	-	-	-	-	-	
38	2	120	-	-	-	-	-	-	-	-	-	-	

Specification

Stainless steel AISI 301

- Plain finish
- Tumbled
- Zinc plated
- Black passivated



BL

● SW

RoHS

Key rings GN 111.3 are suitable as universal connection elements for traction cables, ball chains, retaining straps etc. where light loads are possible. The black design is visually discreet and is also used in situations where the reflections on the surface are to be minimized.

The locking pins and ball lock pins listed in the table have location holes, which the key rings are threaded into. Furthermore, key rings can also be used to supplement retaining cables and ball chains. Thus, it is very easy to secure several elements at the same time from any loss.

The details on load-bearing capacity are guide values given without warranty.

see also...

	Page
GN 111 Ball Chains	QVX
GN 111.5 Ball Chains (Stainless Steel)	QVX
GN 111.2 Retaining Cables (Stainless Steel)	QVX
GN 111.4 Spiral Retaining Cables	QVX

Technical Information

Stainless Steel Characteristics	QVX
---------------------------------	-----

How to order

GN 111.3-24-SW

1 d₁

2 Finish