



elesa  
Original design MFT

| <sup>1</sup> l <sub>1</sub> | <sup>2</sup> d <sub>1</sub> | <sup>2</sup> d <sub>2</sub> | b <sub>1</sub> | b <sub>2</sub> | b <sub>3</sub> | h <sub>1</sub> | h <sub>2</sub> | l <sub>2</sub> ±0,5 | l <sub>3</sub> | t <sub>1</sub> | t <sub>2</sub> |
|-----------------------------|-----------------------------|-----------------------------|----------------|----------------|----------------|----------------|----------------|---------------------|----------------|----------------|----------------|
| 108                         | M 5                         | B 4,5                       | 60             | 26,5           | 11             | 20,5           | 17,5           | 71                  | 91             | 12             | 15,5           |

### Specification <sup>3</sup>

#### Handle

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature -30 °C to +100 °C
- Black-gray, RAL 7021, matte finish ● SG

#### Threaded bushing

Brass

RoHS

Ledge handles GN 130.3 with bore B 4,5 are intended for fastening with tapping screws of thread size ST 4,8, such as pan head self-tapping screws DIN ISO 7049.

#### see also...

|                                  | Page |
|----------------------------------|------|
| GN 130.2 Ledge Handles (Plastic) | QVX  |
| GN 730 Ledge Handles (Aluminum)  | QVX  |
| GN 430 Ledge Handles (Aluminum)  | QVX  |

#### Technical Information

|                         |     |
|-------------------------|-----|
| Strength Properties     | QVX |
| Plastic Characteristics | QVX |

#### How to order

<sup>1</sup> <sup>2</sup> <sup>3</sup>  
GN 130.3-108-B4,5-SG

|   |                                  |
|---|----------------------------------|
| 1 | l <sub>1</sub>                   |
| 2 | d <sub>2</sub> (d <sub>1</sub> ) |
| 3 | Color                            |