


- 1** Type
- DK** With triangular spindle
  - VK7** With square spindle
  - VK8** With square spindle



**2**

Latch arm distance **A**

4	6	8	10	13	14	16	18	20	22	24	26	28	30	32
---	---	---	----	----	----	----	----	----	----	----	----	----	----	----

**Specification**

- Lock housing  
Zinc die casting
- Housing collar  
Powder coated  
Black, RAL 9005, textured finish ● **SW**
- Other parts  
Steel  
Zinc plated, blue passivated
- RoHS

**Accessories**

- Socket Keys GN 119.2 → Page 1266
- Protective Caps GN 120 → Page 1268
- Opening Handles GN 120.1 → Page 1269
- Protective Guide Plates GN 120.2  
→ Page 1270
- Sheet metal punches GN 123 → Page XYZ

**3**

**Information**

Latches GN 115.9 have a **push-to-turn** safety function. In the two end positions the spindle is locked in place by the latch arm. The device can be turned 90° only when the operating element is pressed down with the socket key, which releases the safety pin from the locked position. This feature protects the latch reliably from moving on its own or as the result of vibrations.

The bevels of the latch arm ease the closing of the door. Latch arms are available with different bend angles to cover a latch arm distance A from 4 to 32 mm.

Latches GN 115.9 are supplied with loosely enclosed latch arm.

see also...

- Construction and Assembly Instructions → Page 1201
- List of Latch Types → Page 1196 ff.

How to order

**GN 115.9-DK-32-SW**

<b>1</b>	Type
<b>2</b>	Latch arm distance A
<b>3</b>	Finish (Housing collar)

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9

