



**Rostfrei**®  
Inox  
Stainless  
Steel

**4 Type**

**A** Without bores

**2**

**3**

$l_1$	$l_2$	$d$	$h$	$s$
60	30	6	12	3
60	40	6	12	3
60	60	6	12	3
80	30	6	12	3
80	40	6	12	3
80	80	6	12	3
100	100	6	12	3

**Specification**

**1**

**5**

- Stainless steel **NI**
- AISI 304
- Plain **BL**
- Pin
- Stainless steel AISI 304
- Riveted
- Load Rating Information* → Page 2121
- Stainless Steel Characteristics* → Page 2166
- RoHS

**On request**

- Other dimensions
- With bores
- Other surface types

**Information**

Stainless steel sheet metal hinges GN 1362 are distinguished by their universally compatible dimensions. The materials used also permit applications in aggressive environments.

Type A is fastened via welding or holes created by the customer.

Thanks to the standard dimensions, special application-specific solutions can be realized even in relatively small quantities.

see also...

- List of Hinge Types* → Page 1284 ff.
- Sheet Metal Hinges GN 136 (Steel / Stainless Steel)* → Page 1300
- Hinges GN 128 (Steel, for Welding)* → Page 1388
- Stainless Steel Hinges GN 128.2 (for Welding)* → Page 1389
- Hinges GN 1366 (Steel, for Welding)* → Page 1304

**How to order**

<b>1</b>	<b>Material</b>
<b>2</b>	$l_1$
<b>3</b>	$l_2$
<b>4</b>	<b>Type</b>
<b>5</b>	<b>Finish</b>

**GN 1362-NI-60-40-A-BL**