


- 1 Type**
- RG** With knurled knob in plastic GN 7336
 - KG** With wing knob in plastic
 - HG** With lever in plastic
 - SG** With stainless steel star knob
 - KGN** With stainless steel wing knob
 - HGN** With stainless steel lever



2

Latch arm distance **A**

6	10	14	18	20	22	24	26	28	30	34	38	40	50
---	----	----	----	----	----	----	----	----	----	----	----	----	----

Specification

- Lock housing
Stainless steel AISI 303 **NI**
- Latch arm
Stainless steel AISI 304
- Operating elements
 - Type SG
Stainless steel AISI 304
Sheet metal drawn and hub welded
 - Type KGN, HGN
Stainless steel AISI CF-8
 - Type RG, KG, HG
Plastic (Polyamide PA)
Black, matte finish
- Other parts
Stainless steel AISI 304
- Protection class IP 65
Type SG / KGN / HGN
- IP Protection Classes → Page 2153
- Plastic Characteristics → Page 2158
- Stainless Steel Characteristics → Page 2166
- RoHS

3

Information

Stainless steel latches GN 115 lock by a turning operation limited to 90° which moves the latch arm in the locked position behind the door frame. The bevels of the latch arm ease the closing of the door. Thanks to the stainless steel materials used, the latches are optimally suited for use in corrosive environments.

Latch arms are available with different bend angles to cover a latch arm distance A from 6 to 50 mm.

Stainless steel latches GN 115 are supplied with loosely enclosed latch arm.

see also...

- Construction and Assembly Instructions → Page 1201
- List of Latch Types → Page 1196 ff.
- Latches GN 115 (Steel, Zinc Plated, with Operating Elements) → Page 1200
- Stainless Steel Latches GN 115 (Lockable) → Page 1208

How to order

GN 115-SG-18-NI

1	Type
2	Latch arm distance A
3	Material