





Swivelling range



Type A



Type B



Type C

Bores for socket cap screw DIN 912



elasa
Original design CFD.

3 Type

- A** 2x2 threaded blind bores
- B** 2x threaded blind bores
2x threaded studs
- C** 2x threaded blind bores
2x bores
for socket cap screws
- D** 2x2 threaded studs
- E** 2x threaded studs
2x threaded blind bores
- F** 2x threaded studs
2x bores
for socket cap screws

1

2

l_1	l_2	d_1	d_2	d_3	h_1	h_2	h_3	l_3	l_4	l_5	$l_6 \approx$	l_7	l_8	$m_1 \pm 0,2$	$m_2 \pm 0,2$	t_1	t_2
26	30	M 3	3,3	2,5	12,5	9,5	19	22,5	7	15	7,5	13	4	15	15	4	4
34	40	M 4	4,3	4	16,5	12,5	25	29,5	9,5	20	9,3	18	6	20,2	20	5,5	5,5
41	48	M 5	5,5	5	20	15	30	35	11	24	12	17	8	23	24	6,5	6,5
56	66	M 6	6,5	6	27,5	21	42	48,5	15	33	16,7	16	10	31,8	33	9	10

Specification

- Plastic (Polyamide PA)
 - Black, matte finish
 - Temperature resistant up to 80 °C
- Pin
Stainless steel AISI 303
- Threaded bushings
Brass, nickel plated
- Threaded studs
Steel, nickel plated
- *Load Rating Information* → Page 2126
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Information

The hinges GN 154 consist of two different leaves of unequal length. They are preferably used when thick walled doors or door profiles have to be screwed on to thin walled housings.

see also...

- *List of Hinge Types* → Page 1284 ff.

How to order

GN 154-56-66-D

- 1 l_1
- 2 l_2
- 3 Type

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

