




Type DK6,5  
Type DK7



Type VK6  
Type VK7  
Type VK8



Type VDE5



Type SCH



2	Type
DK6,5	With triangle h=6.5
DK7	With triangle h=7
VK6	With square
VK7	With square
VK8	With square
VDE5	With double bit d <sub>2</sub> = 5,6
SCH	With blade / slot

1

l <sub>1</sub>	l <sub>2</sub>	b	d <sub>1</sub>	d <sub>2</sub>	h	s	A/F	Type	for locks
55	34	32	11,4	-	6,5	1,3	6	DK6,5 VK6 -	SCH GN 115.1 / GN 115.6
86	53	50	14	5,6	7	1,8	7	DK7 VK7 VDE5 SCH	GN 115 / GN 115.7 / GN 115.8 / GN 115.10 / GN 116.1 / GN 119 GN 119.3 / GN 515 / GN 516 / GN 516.1 / GN 516.5
86	53	50	14	-	-	-	8	- VK8 - -	GN 115 / GN 115.7 / GN 115.8 / GN 115.10 / GN 116.1 / GN 119 GN 119.3 / GN 515 / GN 516 / GN 516.1 / GN 516.5

Specification

Zinc die casting

Powder coated

Black, RAL 9005, textured finish

● SW

RoHS

How to order

GN 119.2-86-VK8-SW

1	l <sub>1</sub>
2	Type
3	Finish