


Application example



ELESA Original design MSX.

1

2

d₁ Bore B	d₂ Bore B	k	Length l	m	S₁ Square V	S₂ Square V
B 10	B 10	21	52	17	V 8	V 8
B 12	B 12	21	52	17	V 10	V 10
B 14	B 14	21	52	17	V 12	V 12

Specification

- Plastic
Technopolymer (Polyamide)
- glass fibre reinforced
- temperature resistant up to 60 °C
- black, matt
- Socket cap screws DIN 912
Stainless Steel AISI 304
- Hexagon nuts ISO 4032
Stainless Steel AISI 304
- *Plastic characteristics* → Page XYZ ff.
- *Stainless Steel characteristics* → Page XYZ
- **RoHS compliant**

Information

see also...

- *Two-way clamp mountings GN 474 (Aluminium)* → Page XYZ
- *Retaining rods / Retaining tubes GN 480.1* → Page XYZ
- *Construction tubes GN 990* → Page XYZ

How to order

GN 174-B10-B10

1 d₁

2 d₂