



3 Type

- D Straight lever
- E Angled lever

d₁	d₂	d₃	d₄	d₅	h₁	h₂	h₃	h₄ ≈	h₅ Stroke	Length l	t min.
32	M 6 M 8	13,5	8	20	20,5	1,5	12,5	36	4	100	11
36	M 8 M 10	16	10	25	24,5	2	15	45	4,5	120	14
40	M 10 M 12	19	12	30	30	4	19	53	4,5	130	17
45	M 12 M 16	23	12	32	35,5	4	24	64	5	145	22

Specification

Hub / Shaft

Stainless steel AISI 303
Matte shot-blasted

Insert

Stainless steel AISI 303

Cover

Plastic, polyvinyl chloride (PVC-U)
Light gray

Ball knob DIN 319

Plastic, phenolic resin (PF)
Black, shiny finish

Safety circlip

Plastic, polyacetal (POM)

RoHS

On request

- With threaded through hole

The overall height of flat adjustable tension levers GN 125.5 is reduced to a minimum.

As all other adjustable levers, they are ideal whenever parts have to be clamped in a confined space, or a particular lever position is required. The threaded insert is connected with the hub via serrations which can be disengaged.

Pulling the lever, disengages the serrations and the lever can be swivelled to the ideal clamping position. On releasing the lever it will automatically re-engage.

see also...

	Page
GN 126.1 Flat Adjustable Tension Levers (Zinc Die Casting, Insert Stainless Steel)	QVX
GN 125 Flat Adjustable Tension Levers (Steel)	QVX

Technical Information

Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order

GN 125.5-40-M12-E

1	d ₁
2	d ₂
3	Type

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

