



| 1 d min. | 2 d max. | Length l | b |
|-----------------|-----------------|----------|---|
| A 16 | 20 | 110 | 3 |
| A 25 | 28 | 136 | 4 |
| A 30 | 32 | 136 | 4 |
| A 34 | 36 | 170 | 5 |
| A 40 | 42 | 170 | 5 |
| A 45 | 50 | 206 | 6 |
| A 52 | 55 | 206 | 6 |
| A 58 | 62 | 240 | 7 |
| A 65 | 70 | 240 | 7 |
| A 68 | 75 | 240 | 7 |
| A 80 | 90 | 280 | 8 |
| A 95 | 100 | 280 | 8 |

Specification

- Steel blackened
- RoHS compliant

Information

- see also...
- Levelling sets GN 350 → Page 548
 - Levelling sets GN 350.1 → Page 550
 - Levelling sets GN 350.2 → Page 552
 - Levelling sets GN 350.5 → Page 553
 - Levelling sets GN 360 → Page XYZ
 - Slotted locknuts DIN 1804 → Page 532
 - Slotted locknuts GN 1804.1 → Page 533

| | |
|--|-----------------|
| How to order DIN 1810-A34-36 | 1 d min. |
| | 2 d max. |

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

