

$d_1^{+0,2}_{+0,3}$	$d_2 - 0,5$	h	t	for serrated locking plates GN 187.4 - d_0
22	26	14,5	12,5	22
27	31	16,5	14,5	27
32	36	19,5	17,5	32
40	44	24,5	22,5	40

Specification

- Steel **ST**
- Stainless Steel AISI 303 **NI**
- *Stainless Steel characteristics* → Page 1489
- RoHS



Information

- see also...
- *Serrated locking plates GN 187.4* → Page 824

How to order


GN 187.1-27-NI

- | | |
|---|----------|
| 1 | d_1 |
| 2 | Material |

GN 187.2

Stainless Steel-Thrust springs

for serrated locking plates GN 187.4 / GN 189



d	max. spring load in N ≈	for serrated locking plates GN 187.4 - d_0
15	40	22
18	45	27
23	65	32
29	90	40

Specification

- Stainless Steel AISI 301
- *Stainless Steel characteristics* → Page 1489
- RoHS

Information

Thrust springs GN 187.2 are placed between serrated locking plates GN 187.4 or GN 189 and ensure that the locking plates separate reliably when removed.

see also...

- *Serrated locking plates (Steel / Stainless Steel) GN 187.4* → Page 824

How to order

GN 187.2-18

- | | |
|---|---|
| 1 | d |
|---|---|