



4 Type

- D Straight lever
- E Angled lever



| d ₁ | d ₂ | l ₁ | | | | | | | | | d ₃ | d ₄ | d ₅ | h ₁ | h ₂ | h ₃ | h ₄ ≈ | h ₅ Stroke | l ₂ |
|----------------|----------------|----------------|----|----|----|----|----|----|----|------|----------------|----------------|----------------|----------------|----------------|----------------|------------------|--------------------------|----------------|
| 32 | M 8 | 12 | 16 | 20 | 25 | 32 | 40 | 50 | - | 13,5 | 8 | 20 | 20,5 | 1,5 | 12,5 | 36 | 4 | 100 | |
| 36 | M 10 | 16 | 20 | 25 | 32 | 40 | 50 | 63 | 80 | 16 | 10 | 25 | 24,5 | 2 | 15 | 45 | 4,5 | 120 | |
| 40 | M 12 | 25 | 32 | 40 | 50 | 63 | 80 | - | - | 19 | 12 | 30 | 30 | 4 | 19 | 53 | 4,5 | 130 | |
| 45 | M 16 | 32 | 40 | 50 | 63 | 80 | - | - | - | 23 | 12 | 32 | 35,5 | 4 | 24 | 64 | 5 | 145 | |

Specification

Hub / Shaft

Stainless steel AISI 303
Matte shot-blasted

Insert

Stainless steel AISI 303

Cover

Plastic, polyvinyl chloride (PVC-U)
Light gray

Ball knob DIN 319

Plastic, phenolic resin (PF)
Black, shiny finish

Safety circlip

Plastic, polyacetal (POM)

RoHS

The overall height of flat adjustable tension levers GN 125.5 is reduced to a minimum.

As all other adjustable levers, they are ideal whenever parts have to be clamped in a confined space, or a particular lever position is required. The threaded insert is connected with the hub via serrations which can be disengaged.

Pulling the lever, disengages the serrations and the lever can be swivelled to the ideal clamping position. On releasing the lever it will automatically re-engage.

see also...

| | Page |
|--|------|
| GN 126.1 Flat Adjustable Tension Levers (Zinc Die Casting, Insert Stainless Steel) | QVX |
| GN 125 Flat Adjustable Tension Levers (Steel) | QVX |

Technical Information

| | |
|---------------------------------|-----|
| Plastic Characteristics | QVX |
| Stainless Steel Characteristics | QVX |

How to order

GN 125.5-32-M8-20-D

- 1 d₁
- 2 d₂
- 3 l₁
- 4 Type

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

