


Rostfrei
 Inch sizes available
 Inox Stainless Steel

- 3 Identification no.**
- 2** with 2 Stainless Steel-Clamping screws DIN 912



1 d_1 Bore B		2 d_2 Bore B		d_3 Clamping thread	k Clamping length	Length l	m	Clamping kit for d_3	
Aluminum	St. Steel	Aluminum	St. Steel					Lever zinc die casting	Lever Stainless Steel
B 10	-	B 10	-	M 6	25	64	20	GN 911-M6-22	GN 911.3-M6-22
B 12	B 12	B 12	B 12	M 6	25	64	20	GN 911-M6-22	GN 911.3-M6-22
B 14	B 14	B 14	B 14	M 6	25	64	20	GN 911-M6-22	GN 911.3-M6-22
B 15	B 15	B 15	B 15	M 6	25	64	20	GN 911-M6-22	GN 911.3-M6-22
B 16	B 16	B 16	B 16	M 6	25	64	20	GN 911-M6-22	GN 911.3-M6-22
B 18	B 18	B 18	B 18	M 6	25	64	20	GN 911-M6-22	GN 911.3-M6-22
-	B 20	-	B 20	M 6	25	64	20	GN 911-M6-22	GN 911.3-M6-22

Specification

- Aluminum
 - plastic coated black, RAL 9005, textured finish **● SW**
 - blank matte shot-blasted **○ BL**
- Stainless Steel AISI CF-8 **NI**
 - matte shot-blasted
- Clamping bores mechanically machined
- Socket cap screws DIN 912 Stainless Steel AISI 304
- Hexagon nuts DIN 985 Stainless Steel AISI 304
- Stainless Steel characteristics → Page 1489
- RoHS

Accessory

- Clamping kits GN 911 / GN 911.3 → Page 1242

On request

- d_1 / d_2 with different bores

Information

The clamping bores of GN 131 two-way connector clamps are mechanically machined and designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462 respectively.

The standard version of the clamping screws are socket cap screws with hexagonal socket DIN 912. They can be replaced by clamping kits GN 911 / GN 911.3 (article code see table of dimensions).

see also...

- Two-way clamp mountings GN 474 → Page 1248
- Construction tubes GN 990 → Page 1277
- Retaining rods / Retaining tubes GN 480.1 → Page 1276
- Linear connectors GN 131.1 / GN 131.2 (for linear actuators) → Page 1330

How to order (Aluminum)	
1	d_1
2	d_2
3	Identification no.
4	Finish

GN 131-B14-B14-2-SW

How to order (Stainless Steel)	
1	d_1
2	d_2
3	Identification no.
4	Material

GN 131-B18-B18-2-NI