



Assembly instruction
Type E



Assembly instruction
Type K / S



2 Type

- E** with eccentric lever
- K** with hand lever
- S** with socket cap screw
DIN 912



d ₁	d ₂	d ₃	d ₄	h ₁	h ₂	h ₃ Stroke	h ₄	h ₅	l ₁	l ₂	s
Locking plate GN 187.5											
27	9	M 5	M 6	16	15	0,9	33	4,6	44	45	12
32	9	M 5	M 6	19	19,3	1,1	33	4,6	63	45	12
40	11	M 6	M 8	24	25,5	1,3	42,5	5,6	82	63	14

Specification

- **Type E**
 - Eccentric lever
Stainless Steel AISI CF-8
 - Contact surface
Stainless Steel AISI 431
- **Type K**
 - Hand lever
Zinc die casting
plastic coated
black, RAL 9005, textured finish
- **Type S**
 - Socket cap screw DIN 912
Stainless Steel A2
- Countersunk screw DIN 7991 / Washer
Stainless Steel A2
- Other parts
Stainless Steel AISI 303
- **RoHS**

Information

Locking joint sets GN 187.6 can be used to combine Stainless Steel-Locking heads GN 187.5 to form locking joints. Thanks to the hexagonal shoulder, which creates a form-locking connection that prevents the part from also turning, the centering bushing allows fast and easy mounting. In the unlocked state, the bushing or draw nut forms the axis that positions the locking heads center to center.

The use of Stainless Steel-Thrust springs GN 187.2 allows the locking heads to be cleanly separated from each other.

The types E and K are used in applications requiring frequent and tool-free adjustment of the locking joints.

see also...

- *Stainless Steel-Locking plates GN 187.5* → *New products*
- *Stainless Steel-Thrust springs GN 187.2* → *Page 827*

How to order

GN 187.6-27-S

- 1** d₁
- 2** Type

