



- 4 Identification no.**
- 2** With 2 stainless steel socket cap screws DIN 912

1 d_1 Bore	2 d_2 Bore	3 k Clamping length	l_1	l_2	m	z Screw locations	Accessory Recom. hand lever GN 911 for z l_3	
B 20	B 20	40	97	40	33	M8-25	-	-
B 25	B 25	40	97	40	33	M8-25	63	78
B 30	B 30	40	97	40	33	M8-25	63	78
B 30	B 30	56	125	56	45	M10-35	-	-
B 32	B 32	56	125	56	45	M10-35	-	-
B 35	B 35	56	125	56	45	M10-35	78	92
B 40	B 40	56	125	56	45	M10-35	78	92
B 40	B 40	65	143	65	53	M10-50	-	-
B 42	B 42	65	143	65	53	M10-50	78	92
B 45	B 45	65	143	65	53	M10-50	78	92
B 48	B 48	65	143	65	53	M10-50	78	92
B 50	B 50	65	143	65	53	M10-50	78	92
B 50	B 50	80	169	80	65	M10-50	-	-
B 60	B 60	80	169	80	65	M10-50	78	92

Specification

- Aluminum
 - Powder coated
Black, RAL 9005, textured finish **● SW**
 - Plain, matte shot-blasted **○ BL**
- Socket cap screws DIN 912
Stainless steel AISI 304
- Hex nuts DIN 985
Stainless steel AISI 304
Self-locking via polyamide ring
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

Accessory

- Adjustable Hand Levers GN 911 → Page 1784

On request

- With inch bores



Information

The clamping bores of two-way connector clamps GN 132 are mechanically machined and designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462.

At the screw locations z , the socket cap screws reduce the bore cross-section for clamping.

For clamping without tools, the socket cap screws can be replaced by the adjustable hand levers GN 911 listed in the table as accessories.

see also...

- *Construction Tubes GN 990* → Page 1835
- *Linear Actuator Connectors GN 132.1 / GN 132.2 (for Linear Actuators)*
→ Page 1955

How to order

1	d_1
2	d_2
3	k
4	Identification no.
5	Finish

GN 132-B30-B30-56-2-BL