



4 Identification no.

2 With 4 stainless steel socket cap screws DIN 912



d ₁ Bore	s ₁ Square	d ₂ Bore	s ₂ Square	k Clamping length	l ₁	l ₂	l ₃	m	z Screw locations	Accessory Recom. hand lever GN 911 for z l ₄	
B 20	V 20	B 20	V 20	50	120	68	46	86	M8-35	63	78
B 25	V 25	B 25	V 25	50	120	68	46	86	M8-35	63	78
B 30	V 30	B 30	V 30	50	120	68	46	86	M8-35	63	78
B 30	V 30	B 30	V 30	60	141	79	59	101,5	M8-50	63	78
B 32	-	B 32	-	60	141	79	59	101,5	M8-50	63	78
B 35	V 35	B 35	V 35	60	141	79	59	101,5	M8-50	63	78
B 40	V 40	B 40	V 40	60	141	79	59	101,5	M8-50	63	78
B 40	V 40	B 40	V 40	76	176	98	70	127	M10-60	78	92
B 42	-	B 42	-	76	176	98	70	127	M10-60	78	92
B 45	V 45	B 45	V 45	76	176	98	70	127	M10-60	78	92
B 48	-	B 48	-	76	176	98	70	127	M10-60	78	92
B 50	V 50	B 50	V 50	76	176	98	70	127	M10-60	78	92

Specification

- Aluminum
 - Powder coated
 - Black, RAL 9005, textured finish ● **SW**
 - Plain finish, matte shot-blasted ○ **BL**
- Socket cap screws DIN 912
 - Stainless steel AISI 304
- Hex nuts DIN 985
 - Stainless steel AISI 304
 - Self-locking via polyamide ring
- Stainless Steel Characteristics → Page 2166
- RoHS

Accessory

- Adjustable Hand Levers GN 911 → Page 1784

Information

The clamping bores of T-angle connector clamps GN 194 are not machined and designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462.

The versions with square bores are also suitable for use with **profile systems**.

At the screw locations **z**, the socket cap screws reduce the bore cross-section for clamping.

For clamping without tools, the socket cap screws can be replaced by the adjustable hand levers GN 911 listed in the table as accessories.

How to order (Bore - Bore)

1	d ₁ (s ₁)
2	d ₂ (s ₂)
3	k
4	Identification no.
5	Finish

GN 194-B42-B42-76-2-BL

How to order (Square - Bore)

1	s ₁ (d ₁)
2	d ₂ (s ₂)
3	k
4	Identification no.
5	Finish

GN 194-V50-B50-76-2-SW

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

