



- 3 Identification no.**
- 2** With 2 stainless steel socket cap screws DIN 912

1 **2**

d_1 Bore	d_2 Bore						k_1 Clamping length	k_2 Clamping length	l_1	l_2	l_3	m	z_1 Screw locations	z_2 Screw locations	Accessory Recom. hand lever	
	B 20	B 10	B 12	B 14	B 15	B 16									B 18	for z_1 l_4
B 20	B 10	B 12	B 14	B 15	B 16	B 18	40	36	81,5	40	26	27	M8-25	M6-20	-	63
B 25	B 10	B 12	B 14	B 15	B 16	B 18	40	36	81,5	40	26	27	M8-25	M6-20	63	78
B 30	B 10	B 12	B 14	B 15	B 16	B 18	40	36	81,5	40	26	27	M8-25	M6-20	63	78
B 40	B 20	B 25	B 30	-	-	-	65	59	122	65	40	45	M10-50	M8-25	92	78
B 42	B 20	B 25	B 30	-	-	-	65	59	122	65	40	45	M10-50	M8-25	78	92
B 45	B 20	B 25	B 30	-	-	-	65	59	122	65	40	45	M10-50	M8-25	78	92
B 48	B 20	B 25	B 30	-	-	-	65	59	122	65	40	45	M10-50	M8-25	78	92
B 50	B 20	B 25	B 30	-	-	-	65	59	122	65	40	45	M10-50	M8-25	78	92
B 50	B 40	B 42	B 45	B 48	-	-	80	65	157	80	59	60	M10-50	M10-50	-	92
B 60	B 40	B 42	B 45	B 48	B 50	-	80	65	157	80	59	60	M10-50	M10-50	78	92

Specification

- Aluminum
 - Powder coated
Black, RAL 9005, textured finish **● SW**
 - Plain, matte shot-blasted **○ BL**
- Socket cap screws DIN 912
Stainless steel AISI 304
- Hex nuts DIN 985
Stainless steel AISI 304
Self-locking via polyamide ring
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Accessory

- Adjustable Hand Levers GN 911 → Page 1784

Information

The clamping bores of two-way connector clamps GN 133 are mechanically machined and designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462.

At the screw locations z_1 / z_2 , the socket cap screws reduce the bore cross-section for clamping.

For clamping without tools, the socket cap screws can be replaced by the adjustable hand levers GN 911 listed in the table as accessories.

see also...

- *Construction Tubes GN 990* → Page 1835

How to order

1	d_1
2	d_2
3	Identification no.
4	Finish

GN 133-B30-B16-2-SW