



4 Sensitivity
30 Angle minutes,
 bubble move by 2 mm

d₁	d₂	d₃ -0,2	h₁	h₂
20	12	18	10	8
25	14	20	12	9
30	20	28	13	10

Specification

Housing

Aluminum

- Anodized, natural color
- Anodized, black

- ALN
- ALS

Spirit level element

- Glass plastic body
- Filling
- Colorless-transparent

K

Casting compound

Mineral-based

RoHS

On request

- Filling, green-transparent
- Other sensitivities
- Housing in brass or stainless steel

Bull's eye spirit levels GN 2278 are used to check the horizontal position of jigs, machines, devices, appliances and instruments.

The housing is grooved at its lower diameter d_3 , making it easier to mount in place, e. g. by gluing.

The spirit levels are aligned in relation to the reference or contact surface, so that the bubble is located inside the marking ring once the horizontal position of the contact surface is reached.

see also...

	Page
GN 2277 Bull's Eye Spirit Levels (with Mounting Flange)	QVX
GN 2281 Bull's Eye Spirits Levels (for Installation in Plates and Housings)	QVX
GN 2279 Bull's Eye Spirit Levels (for Surface Mounting)	QVX
GN 2280 Bull's Eye Spirit Levels (Adjustable)	QVX
GN 2282 Screw-On Spirit Levels (for Mounting with Screws)	QVX

Technical Information

General Information on Bull's Eye, Screw-On and Cross Spirit Levels	QVX
---	-----

How to order

1 Material / Finish
2 d_1
3 Filling
4 Sensitivity

GN 2278-ALS-25-K-30

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

