




Type A

Type B

Type C



**4 Type**

- A** without bores (only in Stainless Steel NI)
- B** with through-holes
- C** with countersunk holes

<b>2</b> $l_1$		<b>3</b> $l_2$	$d_1$	$d_2$	$d_3$	$d_4$	$m_1$	$m_2$	$m_4$	$m_5$	$s$
on one side elongated	on both sides elongated										
45	-	30	3	3,2	4	6,4	33	18	9	24	1,5
-	60	30	3	3,2	4	6,4	48	18	9	24	1,5
60	-	40	4	4,2	5	8,3	45	25	12,5	32,5	2
-	80	40	4	4,2	5	8,3	65	25	12,5	32,5	2
75	-	50	6	5,2	5	8,3	55	30	15	40	2
-	100	50	6	5,2	5	8,3	80	30	15	40	2
90	-	60	6	5,2	5	8,3	66	36	18	48	2
-	120	60	6	5,2	5	8,3	96	36	18	48	2

**Specification**

- Steel **ST**
  - only type B and C
  - zinc plated, blue passivated
- Stainless Steel AISI 304 **NI**
  - all types
- Pin
  - Stainless Steel AISI 304
  - riveted
- *Stainless Steel characteristics* → Page 1489
- *Load rating information* → Page 1459
- RoHS

**Information**

GN 136 sheet metal hinges are available in many different versions and are suitable for light to medium-duty applications.

Type A can be fixed in place by welding or by using holes made by the customer.

see also...

- *List of hinge types* → Page 956 ff.
- *Sheet metal hinges GN 136 (square or vertically elongated)* → Page 965

<b>How to order</b>		<b>1</b> Material
<b>1</b>	<b>2</b>	<b>3</b>
<b>GN 136-ST-60-40-B</b>		<b>4</b> Type

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9

