



## Mounting holes - outer slide



$l_1$	$a_2$	$a_3$	$a_4$	$a_5$
300	113,5	209,5	273,5	-
350	113,5	209,5	337,5	-
400	113,5	209,5	369,5	-
500	145,5	209,5	337,5	465,5

## Mounting holes - inner slide



$l_1$	$i_3$	$i_4$	$i_5$
300	142,5	182,5	-
350	167,5	207,5	-
400	192,5	232,5	282,5
500	242,5	282,5	357,5

## Fastening screws

For the said loading forces  $F_S$  to be absorbed reliably in the surrounding structure, all available through-holes of the outer and inner slide must be used. Failure to use fastening screws reduces the specified load capacity accordingly. The following screws can be used for mounting:

Designation - standard		Outer slide	Inner slide
Countersunk screw, Phillips	DIN 965	M 4	M 4
Countersunk screw, Phillips	DIN 7997	Size 3,5 / 4	Size 3,5