



**4 Sensitivity**

30 Angle minutes, bubble move by 2 mm

**5 Type**

- A With smooth reference surface
- B With mounting thread

**2**

| d <sub>1</sub> | d <sub>2</sub> | d <sub>3</sub> | h <sub>1</sub> | h <sub>2</sub> | h <sub>3</sub> |
|----------------|----------------|----------------|----------------|----------------|----------------|
| 14             | 10             | M 4            | 9,5            | 7,7            | 5              |
| 20             | 14             | M 5            | 13             | 13             | 6              |
| 30             | 21             | M 6            | 15             | 15             | 7,5            |

**Specification**

**Housing**

- Aluminum
- Anodized, natural color
- Anodized, black

- ALN
- ALS

**Spirit level element**

- Glass plastic body
- Filling
- Colorless-transparent

**K**

**Casting compound**

Mineral-based

RoHS

**On request**

- Filling, green-transparent
- Other sensitivities
- Housing in brass or stainless steel

Bull's eye spirit levels GN 2279 are used to check the horizontal position of jigs, machines, devices, appliances and instruments.

Type A is used if the spirit level is to be used as a tool, e.g. at different measuring points.

The spirit levels are aligned in relation to the reference or contact surface, such that the bubble is located inside the marking ring once the horizontal position of the contact surface is reached.

**see also...**

|  | Page |
|--|------|
| GN 2280 Bull's Eye Spirit Levels (Adjustable)                    | QVX  |
| GN 2277 Bull's Eye Spirit Levels (with Mounting Flange)          | QVX  |
| GN 2278 Bull's Eye Spirit Levels (for Insertion into Bore Holes) | QVX  |
| GN 2276 Cross Spirit Levels (for Mounting with Screws)           | QVX  |

**Technical Information**

General Information on Bull's Eye, Screw-On and Cross Spirit Levels

Information générale sur les niveaux à bulle ronds, horizontaux et croisés QVX

**How to order**

|   |                   |
|---|-------------------|
| 1 | Material / Finish |
| 2 | d <sub>1</sub>    |
| 3 | Filling           |
| 4 | Sensitivity       |
| 5 | Type              |

**GN 2279-ALS-20-K-30-A**

