



ELESA original design CFD.

Swivelling range




3 Type


- A** 2x2 threaded blind bores
- B** 2x threaded blind bores / 2x threaded studs
- C** 2x threaded blind bores / 2x bores for socket head cap screws
- D** 2x2 threaded studs
- E** 2x threaded studs / 2x threaded blind bores
- F** 2x threaded studs / 2x bores for socket head cap screws




Type A




Type B




Type C



Type D



Type E



Type F

1

2

l_1	l_2	d_1	d_2	d_3	h_1	h_2	l_3	l_4	l_5	l_6	l_7	l_8	m_1 $\pm 0,2$	m_2 $\pm 0,2$	t_1	t_2
26	30	M 3	3,3	2,5	12,5	9,5	22,5	7	15	8	12	4	15	15	4	4
34	40	M 4	4,3	4	17	12,5	29	9,5	20	9	18	6	20	20	5,5	5,5
41	48	M 5	5,5	5	20	15	35	11	24	12	17	8	23	24	6,5	6,5
56	66	M 6	6,5	6	27,5	21	48,5	15	33	16	16	10	32	33	9	10

Specification

- Plastic (Polyamide PA)
 - black, matte
 - temperature resistant up to 80 °C
- Pin
 - Stainless Steel
 - German Material No. 1.4305
- Threaded bushings
 - Brass, nickel plated
- Threaded studs
 - Steel, nickel plated
- Plastic characteristics → Page 1483
- Stainless Steel characteristics → Page 1489
- Load rating information → Page XYZ
- RoHS compliant

Information

The hinges GN 154 consist of two different wings of unequal length. They are preferably used when thick walled doors or door profiles have to be screwed on to thin walled housings.

How to order

GN 154-56-66-D

1	l_1
2	l_2
3	Type

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

