



- 2 Type**
U for floating bearing rails
X for fixed bearing rails



h_1 Rail	b_1	b_2	d for cylinder head screw DIN 912	h_2	l_1	l_2	l_3 max.	m_1	m_2
18	12,6	5,6	M 3	17	7	5	3,5	-	3,5
28	19	10	M 4	25	7	5	3,5	8	4,5
35	25,5	12,5	M 4	32	7	5	3,5	10	5,5
43	32,2	15	M 4	40	7	5	3,5	12	7,5

Specification

- Wiper
Plastic PUR, gray
- Bracing core
Steel, zinc plated
- Cylinder head screw DIN 912
Steel
zinc plated, blue passivated
- RoHS

Information

Wipers GN 2428 protect against dirt deposits on rails and rollers.
 For size $h_1 = 18$ the wiper is attached with only one central screw.
 Screws are included parts of the order.

see also...

- *Cam roller linear guide rails GN 2422* → Page 1301
- *Cam roller carriages GN 2424* → Page 1302
- *Cam rollers GN 2426* → Page 1304

How to order

GN 2428-35-X

- 1 h_1
- 2 Type

