




Ø2^{H12} x 4
Hole for pin
for swivel limiting stop



Bore for
socket cap screw
DIN 912-M4

Application example



Side thrust pin
GN 614.1



h	b ±0,1	for GN 614				for GN 615 / GN 615.2 / GN 615.3			
		Size	d	w	s min.	Size	d	w	s min.
8,5	3,4	6	5	1,6	0,9	M 8	4,5	1,5	0,8
10,5	4,5	8	6,5	1,9	1	M 10	6	2	1

Specification

- Sintered Steel
 - case hardened
 - blank
- RoHS

Information

Indent blocks GN 250 are used together with spring plungers for detent or positioning of sliders, flaps and similar applications.

see also...

- Spring plungers GN 614 → Page 722
- Spring plungers GN 615 → Page 718
- Plastic-Spring plungers GN 615.2 → Page 720
- Spring plungers GN 615.3 → Page 719
- Side thrust pins GN 614.1 → Page 738

How to order

GN 250-8,5

1 h

