



3 Type

- A without sealing
- B with sealing

1 2

d ₁ Bore B	k Clamping length	d ₂	d ₃ Clamping thread	d ₄	Length l	m	t	x ₁	x ₂	y ₁	y ₂
B 30	50	6,5	M 8	37	36	35	6,5	60	42	60	42
B 50	85	10,7	M 10	60	48,5	60	9	105	74	105	74

Specification

- Stainless Steel
 - AISI CF-8
 - matte shot-blasted
- Clamping bores mechanically machined
- Carriage bolt DIN 603 Stainless Steel A2
- Cap nuts DIN 917 Stainless Steel A2
- Sealings
 - Washers Plastic (Polyacetal POM)
 - Edge ring Silicon, 40 ... 60 Shore A
- *Stainless Steel characteristics* → Page 1489
- RoHS

Information

The clamping bores of GN 163.5 Stainless Steel-Base plate connector clamps are mechanically machined and designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462 respectively.

The shape of the clamping screws / nuts prevents the formation of wetness due to dammed-up water. The designs with sealing (Type B) also seals bore holes and threads.

see also...

- *Stainless Steel-Construction tubes GN 990* → Page 1277
- *Stainless Steel-Base plate connector clamps GN 162 (Bore-Ø B12 ... B20)* → Page 1200
- *Stainless Steel-Base plate connector clamps GN 162.3 (Bore-Ø B12 ... B20)* → Page 1201

How to order

GN 163.5-B30-50-B

- 1 d₁
- 2 k
- 3 Type

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9