


Type **OZ**



Type **AV**




2 Type

OZ Without centring step (smooth)


MZ With centring step

AV With external serration

IV With internal serration



Type **MZ**



Type **IV**

1

b Swivel width	d ₁	d ₂	Length l	m ₁	m ₂	t ₁	t ₂	s	x ₁	x ₂	y ₁	y ₂
40	8,5	6,5	52,5	32,5	30	20	7	13	60	42	60	42
65	10,2	11	84,5	52	52,5	32,5	14	17	105	74	105	74

Specification

- Aluminum
 - Powder coated
 - Black, RAL 9005, textured finish **● SW**
 - Plain, matte shot-blasted **○ BL**
- RoHS

3

Information

Swivel clamp connector bases GN 272 can be combined with swivel clamp connectors GN 274, GN 276 or GN 278 to swivel clamp connector joints.

see also...

- Swivel Clamp Connector Joints GN 282
(Connection of GN 272 with GN 276) → Page 1764
- Sensor Holders GN 272.4 → Page 1777

How to order

GN 272-40-OZ-BL

1	b
2	Type
3	Finish