



- 2 Type**
 - OZ** Without centring step (smooth)
 - MZ** With centering step
 - AV** With external serration
 - IV** With internal serration
- 3 Identification no.**
 - 2** With stainless steel socket cap screw DIN 912

d₁ Bore	b Swivel width	d₂	k	l₁	l₂	m	s	t	z Screw location	Accessory recom. hand lever GN 911 for z l ₃	
B 20	40	8,5	42,5	92	52	72	13	20	M8-25	-	-
B 25	40	8,5	42,5	92	52	72	13	20	M8-25	63	78
B 30	40	8,5	42,5	92	52	72	13	20	M8-25	63	78
B 40	65	10,5	74	148	77,5	115	17	32,5	M10-50	-	-
B 42	65	10,5	74	148	77,5	115	17	32,5	M10-50	-	-
B 45	65	10,5	74	148	77,5	115	17	32,5	M10-50	78	92
B 48	65	10,5	74	148	77,5	115	17	32,5	M10-50	78	92
B 50	65	10,5	74	148	77,5	115	17	32,5	M10-50	78	92

Specification

- Aluminum
 - Powder coated
 - Black, RAL 9005, textured finish ● **SW**
 - Plain, matte shot-blasted ○ **BL**
- Socket cap screws DIN 912
Stainless steel AISI 304
- Hex nuts DIN 985
Stainless steel AISI 304
Self-locking via polyamide ring
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

Accessory

- Adjustable Hand Levers GN 911 → Page 1784

Information

The clamping bore of swivel clamp connectors GN 276 is mechanically machined and designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462.

At the screw location **z**, the socket cap screw reduces the bore cross-section for clamping. For clamping without tools, the socket cap screw can be replaced by an adjustable hand lever GN 911 listed in the table as accessory.

Swivel clamp connectors GN 276 can be combined with swivel clamp connectors GN 272, GN 274 or GN 278 to swivel clamp connector joints.

see also...

- *Construction Tubes GN 990* → Page 1835
- *Swivel Clamp Connector Joints GN 284 (Assembly of GN 274 with GN 276)* → Page 1767
- *Side Mounting Top Brackets GN 87* → Page 1817

How to order	1 d ₁
	2 Type
	3 Identification no.
	4 Finish

GN 276-B30-OZ-2-BL