

3.1

3.2

1

2

d ₁	d ₂ n6	d ₃	d ₄ Diameter of counterbore	Length l
6	10	12,5	13,5	8
8	12	15	16	10
10	15	19	20,6	12

3.3

Specification

- Steel
Hardened (HRC 60 ±2)
- ISO Fundamental Tolerances → Page 2151
- RoHS

Information

Guide bushings GN 172.1 / GN 179.1 with conical bore will be used for the latch bore of indexing plungers GN 817.5.



3.4

How to order (Without collar)

GN179.1-10-15

- | | |
|---|----------------|
| 1 | d ₁ |
| 2 | d ₂ |

3.5



3.6

3.7

1

2

3 Type

A Bore one-sided

d ₁ F7	l ₁		d ₂ n6	d ₃	l ₂
B 6	10	16	10	13	3
B 8	10	16	12	15	3
B 10	12	20	15	18	3

3.8

3.9

Specification

- Steel
Hardened (HRC 62 ±2)
- ISO Fundamental Tolerances → Page 2151
- RoHS

Information

The dimensions stated above are merely an excerpt from the standards DIN 172 / DIN 179 → Page 1112.

How to order (With collar)

DIN 172-B8-16-A

- | | |
|---|----------------|
| 1 | d ₁ |
| 2 | l ₁ |
| 3 | Type |

