



d₁	d₂	b	d₃ ^{+0.2 +0.5}	Length l	m	s	t	Countersunk screw DIN 7991	For cabinet U-handles
8	M 4	10	4	20	10	3	7	M 4 x 10	GN 425-8-...
10	M 5	12	5	24	12	4	8	M 5 x 12	GN 425-10-... / GN 425.1-10-...
12	M 6	15	6	30	15	4,5	9,5	M 6 x 14	GN 425-12-... / GN 425.1-12-... / GN 435-12-...
16	M 6	18	6	34	16	4,5	9,5	M 6 x 14	GN 425-16-... / GN 435-16-...
20	M 6	22	6	40	18	4,5	9,5	M 6 x 14	GN 565-20-... / GN 565.5-20-...
20	M 8	22	8	42	20	6	12	M 8 x 18	GN 426-20-... / GN 426.1-20-...
26	M 8	28	8	52	24	6	12	M 8 x 18	GN 565-26-...
28	M 10	30	10	56	26	6,5	13,5	M 10 x 20	GN 426-28-... / GN 426.1-28-...

Specification

Fastening plates

Zinc die casting
Powder coated

ZD

- Black, RAL 9005, textured finish
- Silver, RAL 9006, textured finish

- **SW**
- **SR**

Countersunk screws DIN 7991

Steel

Zinc plated, blue passivated

RoHS

Fastening sets GN 181 make it possible to mount different cabinet U-handles and tubular handles with internal thread from the operator's side.

The mounting position of the fastening plates is freely customizable, allowing a sideways offset or mounting with different drillhole spacings.

A fastening set consists of two fastening plates and two countersunk screws.

see also...

Page

GN 425 Cabinet U-Handles (Steel / Aluminum / Stainless Steel)	QVX / QVX
GN 425.1 Cabinet U-Handles (Steel / Aluminum / Stainless Steel)	QVX / QVX
GN 435 Cabinet U-Handles (Stainless Steel, Tall Design)	QVX
GN 565 Cabinet U-Handles (Aluminum)	QVX
GN 565.5 Cabinet U-Handles (Stainless Steel)	QVX
GN 426 Cabinet U-Handles (Aluminum)	QVX
GN 426.1 Cabinet U-Handles (Aluminum)	QVX

How to order

1	Material
2	d ₁
3	d ₂
4	Color

GN 181-ZD-28-M10-SW

