




Type K



Type S



Assembly instruction



2 Type

K with adjustable hand lever
S with socket head cap screw
DIN 912



d_1 Locking plate GN 187.5	d_2	d_3	h_1	h_2	h_3	Length l	s
27	M 6	9	33	16	4,6	45	12
32	M 6	9	33	19	4,6	45	12
40	M 8	11	42,5	24	5,6	63	14

Specification

- Handle
Zinc die casting
plastic coated
silver, RAL 9006, textured finish
- Threaded insert and retaining screw
Stainless Steel AISI 303
- Socket cap screw DIN 912
Stainless Steel A2
- Centering threaded bushing
Stainless Steel AISI 304
- Washer
Stainless Steel A2
- *Stainless Steel characteristics* → Page 1489
- **RoHS**

Information

Locking joint sets GN 187.6 can be used to combine Stainless Steel-Locking heads GN 187.5 to form locking joints. Thanks to the hexagonal shoulder, which creates a form-locking connection that prevents the part from also turning, the centering threaded bushing allows fast and easy mounting. In the unlocked state, it forms the axis that positions the locking heads center to center.

The use of Stainless Steel-Thrust springs GN 187.2 allows the locking heads to be cleanly separated from each other.

Type K is used in applications requiring frequent and tool-free adjustment of the locking joints.

The parts of the respective type are delivered loose in the set.

see also...

- *Stainless Steel-Locking plates GN 187.5* → New products
- *Stainless Steel-Thrust springs GN 187.2* → Page 827

How to order

GN 187.6-27-S

1 d_1

2 Type

