



- 3 Identification no.
- 2 with two Stainless Steel-Clamping screws DIN 912

d <sub>1</sub> Bore B		d <sub>2</sub> Bore B		d <sub>3</sub> Clamping thread	k Clamping length	l <sub>1</sub>	l <sub>2</sub>	m	Clamping kit for d <sub>3</sub>	
Aluminum	Stainless Steel	Aluminum	Stainless Steel						Lever zinc die casting	Lever Stainless Steel
B 10	-	B 10	-	M 6	25	61	34,5	39	GN 911-M6-22	GN 911.3-M6-22
B 12	B 12	B 12	B 12	M 6	25	61	34,5	39	GN 911-M6-22	GN 911.3-M6-22
B 14	B 14	B 14	B 14	M 6	25	61	34,5	39	GN 911-M6-22	GN 911.3-M6-22
B 15	B 15	B 15	B 15	M 6	25	61	34,5	39	GN 911-M6-22	GN 911.3-M6-22
B 16	B 16	B 16	B 16	M 6	25	61	34,5	39	GN 911-M6-22	GN 911.3-M6-22
B 18	B 18	B 18	B 18	M 6	25	61	34,5	39	GN 911-M6-22	GN 911.3-M6-22
-	B 20	-	B 20	M 6	25	61	34,5	39	GN 911-M6-22	GN 911.3-M6-22

**Specification**

- Aluminum
  - plastic coated
  - black, RAL 9005, textured finish ● **SW**
  - blank ○ **BL**
  - matte shot-blasted
- Stainless Steel **NI**
  - AISI CF-8
  - matte shot-blasted
- Clamping bores mechanically machined
- Socket cap screws DIN 912  
Stainless Steel AISI 304
- Hexagon nuts DIN 985  
Stainless Steel AISI 304
- *Stainless Steel characteristics* → Page 1489
- **RoHS**

**Accessory**

- Clamping kits GN 911 / GN 911.3  
→ Page 1242

**On request**

- d<sub>1</sub> / d<sub>2</sub> with different bores

**Information**

The clamping bores of GN 191 T-Angle connector clamps are mechanically machined and designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462 respectively.

The standard version of the clamping screws are socket cap screws with hexagonal socket DIN 912. They can be replaced by clamping kits GN 911 / GN 911.3 (article code see table of dimensions).

see also...

- *Construction tubes GN 990* → Page 1277
- *T-Angle linear actuator connectors GN 191.1* → Page 1336

How to order (Aluminum)	1 d <sub>1</sub>
	2 d <sub>2</sub>
<b>GN 191-B12-B12-2-SW</b>	3 Identification no.
	4 Finish

How to order (Stainless Steel)	1 d <sub>1</sub>
	2 d <sub>2</sub>
<b>GN 191-B16-B16-2-NI</b>	3 Identification no.
	4 Material