



¹ l ₁	² d ₁	³ l ₂						d ₃	d ₄	h ₁	h ₃	h ₄ Stroke
63	M 6	20	27	-	-	-	-	24	17,5	34,5	48,5	4
78	M 8	21	36	-	-	-	-	25	21	39,5	58,5	4
92	M 10	29	47	-	-	-	-	30	24	46,5	68,5	4
108	M 12	34	50	57	65	85	-	35	30	56,5	82	5

Specification

- Handle
Zinc die casting
- Plastic coated
black, RAL 9005, textured finish ● **SW**
black, RAL 9011, silk finish ● **SZ**
orange, RAL 2004, textured finish ● **OS**
red, RAL 3000, textured finish ● **RS**
silver, RAL 9006, textured finish ● **SR**
- chrome-plated ● **CR**
- Threaded stud and bushing
Steel
- Tensile strength class 5.8
- nitrided, blackened
- Retaining screw
Steel, blackened
- Strength values of screws → Page 1481
- RoHS

Information

Adjustable hand levers GN 300.4 are produced with a clamping area which is linked via a thrust ball bearing (axial bearing) to the bushing and threaded stud of the hand lever. This has led to the following advantages:

- **Doubled** clamping force through vastly reduced friction.
- There is no movement on the contact area between adjustable handlever and component which greatly reduces any marking on the clamping area.
- In addition a reduced creep factor has been achieved by the increased preload.

How to order

¹	l ₁
²	d ₁
³	l ₂
⁴	Color (Finish)

GN 300.4-92-M10-47-RS