



- 4 Identification no.**
- 2** With 2 stainless steel socket cap screws DIN 912

d ₁ Bore	d ₂ Bore	k ₁ Clamping length	k ₂ Clamping length	l ₁	l ₂	m	z ₁ Screw location	z ₂ Screw location	Accessory Recom. hand lever GN 911			
									for z ₁ l ₃		for z ₂ l ₃	
B 20	B 20	40	42,5	92	52	60	M8-25	M8-25	-	-	-	-
B 25	B 25	40	42,5	92	52	60	M8-25	M8-25	63	78	78	-
B 30	B 30	40	42,5	92	52	60	M8-25	M8-25	63	78	63	78
B 30	B 30	56	62	130	68	90	M10-35	M10-35	-	-	-	-
B 32	B 32	56	62	130	68	90	M10-35	M10-35	-	-	-	-
B 35	B 35	56	62	130	68	90	M10-35	M10-35	92	-	-	-
B 40	B 40	56	62	130	68	90	M10-35	M10-35	78	92	92	-
B 40	B 40	65	75	148	77,5	103	M10-50	M10-50	92	-	-	-
B 42	B 42	65	75	148	77,5	103	M10-50	M10-50	78	92	-	-
B 45	B 45	65	75	148	77,5	103	M10-50	M10-50	78	92	92	-
B 48	B 48	65	75	148	77,5	103	M10-50	M10-50	78	92	78	92
B 50	B 50	65	75	148	77,5	103	M10-50	M10-50	78	92	78	92
B 50	B 50	80	80	177	92	125	M10-50	M10-50	-	-	-	-
B 60	B 60	80	80	177	92	125	M10-50	M10-50	78	92	-	-

Specification

- Aluminum
 - Powder coated
 - Black, RAL 9005, textured finish **● SW**
 - Plain finish, matte shot-blasted **○ BL**
- Socket cap screws DIN 912
Stainless steel AISI 304
- Hex nuts DIN 985
Stainless steel AISI 304
Self-locking via polyamide ring
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

Accessory

- Adjustable Hand Levers GN 911 → Page 1784

On request

- d₁ / d₂ with unequal bores

Information

The clamping bores of T-angle connector clamps GN 192 are mechanically machined and designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462.

At the screw locations z₁ / z₂ the socket cap screws reduce the bore cross-section for clamping.

For clamping without tools, the socket cap screws can be replaced by the adjustable hand levers GN 911 listed in the table as accessories.

see also...

- *T-Angle Connector Clamps GN 81 (Plastic)* → Page 1815
- *Construction Tubes GN 990* → Page 1835
- *T-Angle Linear Actuator Connectors GN 192.1* → Page 1967

How to order	
1	d ₁
2	d ₂
3	k ₁
4	Identification no.
5	Finish

GN 192-B32-B32-56-2-BL