



- 3 Identification no.
- 2 With 6 stainless steel socket cap screws DIN 912

- 1
- 1
- 2

d Bore	s Square	k Clamping length	l ₁	l ₂	l ₃	m	z Screw locations	Accessory Recom. hand lever GN 911 for z l ₄	
B 20	V 20	50	172	68	46	86	M8-35	63	78
B 25	V 25	50	172	68	46	86	M8-35	63	78
B 30	V 30	50	172	68	46	86	M8-35	63	78
B 30	V 30	60	203	79	59	101,5	M8-50	63	78
B 32	-	60	203	79	59	101,5	M8-50	63	78
B 35	V 35	60	203	79	59	101,5	M8-50	63	78
B 40	V 40	60	203	79	59	101,5	M8-50	63	78
B 40	V 40	76	254	98	70	127	M10-60	78	92
B 42	-	76	254	98	70	127	M10-60	78	92
B 45	V 45	76	254	98	70	127	M10-60	78	92
B 48	-	76	254	98	70	127	M10-60	78	92
B 50	V 50	76	254	98	70	127	M10-60	78	92

Specification

- Aluminum
 - Powder coated
 - Black, RAL 9005, textured finish ● **SW**
 - Plain finish, matte shot-blasted ○ **BL**
- Socket cap screws DIN 912
Stainless steel AISI 304
- Hex nuts DIN 985
Stainless steel AISI 304
Self-locking via polyamide ring
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

Accessory

- Adjustable Hand Levers GN 911 → Page 1784

Information

The clamping bores of T-angle connector clamps GN 195 are not machined and designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462.

The versions with square bores are also suitable for use with **profile systems**.

At the screw locations **z**, the socket cap screws reduce the bore cross-section for clamping.

For clamping without tools, the socket cap screws can be replaced by the adjustable hand levers GN 911 listed in the table as accessories.

see also...

- *Product Family Standard Parts for Profile Systems* → Page 18
- *Construction Tubes GN 990* → Page 1835

How to order	1 s (d)
	2 k
GN 195-V35-60-2-SW	3 Identification no.
	4 Finish