



1	2	3						d ₃	d ₄	h ₁	h ₃	h ₄ Stroke
63	M 6	20	27	-	-	-	24	17,5	34,5	48,5	4	
78	M 8	21	36	-	-	-	25	21	39,5	58,5	4	
92	M 10	29	47	-	-	-	30	24	46,5	68,5	4	
108	M 12	34	50	57	65	85	35	30	56,5	82	5	

Specification

- Handle
Zinc die casting
- Powder coated
 - Black, RAL 9005, textured finish ● **SW**
 - Black, RAL 9011, silk finish ● **SZ**
 - Orange, RAL 2004, textured finish ● **OS**
 - Red, RAL 3000, textured finish ● **RS**
 - Silver, RAL 9006, textured finish ● **SR**
- Chrome plated ● **CR**
- Threaded stud and bushing
Steel
 - Property class 5.8
 - Nitrided, blackened
- Retaining screw
Steel, blackened
- *Strength Values of Screws → Page 2152*
- **RoHS**

Information

Adjustable hand levers GN 300.4 are produced with a clamping area which is linked via a thrust ball bearing (axial bearing) to the bushing and threaded stud of the hand lever. This has led to the following advantages:

- **Doubled** clamping force through vastly reduced friction.
- There is no movement on the contact area between adjustable handlever and component which greatly reduces any marking on the clamping area.
- In addition a reduced creep factor has been achieved by the increased preload.

How to order		1	l ₁
		2	d ₁
GN 300.4-92-M10-47-RS		3	l ₂
		4	Color (Finish)

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4