



- 3 Type**
- A** Without scale
  - AS** With scale 0...50, 60 graduations

<b>1</b> $d_1$	<b>2</b> $d_2$ H7 Bore with keyway			$d_3$	$d_5$	$d_6$ P.C.D. Ø for fixing screws Page XYZ	$l_1$	$l_2$	$l_3$ Bore length Page XYZ	$w$ Stroke
44	K 10	K 12	-	33	23	33	37	6	31	4
52	K 12	K 14	K 16	42	31,5	41,8	37,5	6	31,5	4

**Specification**

Stainless steel AISI 303

**4**  
**NI**

- Scale for type AS:
  - laser-engraved, black
  - Reference line on location ring
- Keyway
  - Tolerance slot width P9
  - Bore K 10: DIN 6885-1
  - Bore K 12 ... K 16: DIN 6885-2

RoHS

**On request**

- Special graduations (see „How to Order Graduations“)

Indexing mechanisms GN 200 replace and simplify complicated indexing and safety mechanisms.

Besides the standard scale (Type AS) the control knob version may be supplied with any scale.

Regarding design, numbering run, numbering position and numbering sequence of the scale please see the layout for scale rings on the order sheet „How to Order Graduations“.

see also...	Page
GN 200 Indexing Mechanisms (Steel)	QVX

**Technical Information**

Technical instructions	QVX
How to order - Graduations	QVX
Keyway P9 DIN 6885-1	QVX
Keyway P9 DIN 6885-2	QVX
ISO Fundamental Tolerances	QVX
Stainless Steel Characteristics	QVX

How to order

**1** **2** **3** **4**  
**GN 200-52-K12-AS-NI**

<b>1</b>	$d_1$
<b>2</b>	$d_2$
<b>3</b>	Type
<b>4</b>	Material

