


3 Type

AS With external hexagon

IS With internal hexalobular



1

2

2

1 l_1	2 d_1 Thread				2 d_2 H7 Bore	d_3	d_4	h_1	h_2	h_3	h_4 Stroke	t min.
30	M 3	-	-	-	-	10	13	24,5	4	31	3,5	7
30	M 4	M 5	M 6	B 5	B 6	10	13	24,5	4	31	3,5	8
45	M 4	M 5	M 6	B 5	B 6	10	13	24,5	4	34	3,5	8
63	M 6	M 8	-	B 8	-	13,5	17,5	31	6,5	45	4	11
78	M 8	M 10	M 12	B 8	B 10	16	21	36	8	54	4	14
92	M 10	M 12	-	B 12	-	19	24	43	11	64	4	17

Specification

GN 300.5

- Handle
- Precision casting
- Stainless steel AISI CF-8
- Matte shot-blasted

GN 300.6

- Handle
- Precision casting
- Stainless steel AISI CF-8
- Polished

- Bushing
Stainless steel AISI 303
- Retaining screw
Stainless steel AISI 303
- Pressure spring
Stainless steel AISI 301
- ISO Fundamental Tolerances → Page 2151
- Stainless Steel Characteristics → Page 2166

• RoHS

On request

- With inch threads

Information

Adjustable hand levers GN 300.5 / GN 300.6 with solid stainless steel handle, correspond to applications where „aggressive“ surrounding conditions are given, or where stainless steel materials are prescribed such as in food processing or chemical industry.

Retaining screws with hexagon head (Type AS) comply with the requirement „prevents water from accumulating“.

Adjustable hand levers have proved to be ideal whenever parts have to be clamped in a confined space or in a particular lever position. The centre insert is connected to the lever via serrations which can easily be disengaged.

Pulling the lever, disengages the serrations and allowing it to be swivelled to the ideal clamping position. On releasing the lever the serrations automatically re-engage.

How to order (Matte shot-blasted)	1 l_1
	2 d_1
GN 300.5-78-M10-AS	3 Type

How to order (Polished)	1 l_1
	2 d_1
GN 300.6-92-M12- IS	3 Type