


ROSTFREI Rost free  
Inox Stainless Steel  
Inch sizes available

**3 Type**  
AS with external hexagon  
IS with internal hexalobular



**1** **2** **3**

<b>l<sub>1</sub></b>	<b>d<sub>1</sub></b> Thread			<b>d<sub>2</sub> H7</b> Bore		<b>d<sub>3</sub></b>	<b>d<sub>4</sub></b>	<b>h<sub>1</sub></b>	<b>h<sub>2</sub></b>	<b>h<sub>3</sub></b>	<b>h<sub>4</sub></b> Stroke	<b>t</b> min.
30	M 3	-	-	-	-	10	13	24,5	4	31	3,5	7
30	M 4	M 5	M 6	B 5	B 6	10	13	24,5	4	31	3,5	8
45	M 4	M 5	M 6	B 5	B 6	10	13	24,5	4	34	3,5	8
63	M 6	M 8	-	B 8	-	13,5	17,5	31	6,5	45	4	11
78	M 8	M 10	M 12	B 8	B 10	16	21	36	8	54	4	14
92	M 10	M 12	-	B 12	-	19	24	43	11	64	4	17

**Specification**

- GN 300.5**  
Handle  
Precision casting  
- Stainless Steel AISI CF-8  
- matte shot-blasted
- GN 300.6**  
Handle  
Stainless Steel  
Precision casting  
- Stainless Steel AISI CF-8  
- electropolished
- Bushing  
Stainless Steel AISI 303
- Retaining screw  
Stainless Steel AISI 303
- Spring  
Stainless Steel AISI 301
- ISO-Fundamental tolerances → Page 1479
- Stainless Steel characteristics → Page 1489
- RoHS

**Information**

Adjustable hand levers GN 300.5 / GN 300.6 with solid Stainless Steel-Handle, correspond to applications where „agressive“ surrounding conditions are given, or where Stainless Steel materials are prescribed such as in food processing or chemical industry.

Retaining screws with hexagon head (Type AS) comply with the requirement „prevents water from accumulating“.

Adjustable hand levers have proved to be ideal whenever parts have to be clamped in a confined space or in a particular lever position. The centre insert is connected to the lever via serrations which can easily be disengaged.

Pulling the lever, disengages the serrations and allowing it to be swivelled to the ideal clamping position. On releasing the lever the serrations automatically re-engage.

How to order (matte shot-blasted) **1** l<sub>1</sub>  
**2** d<sub>1</sub>  
**3** Type  
**GN 300.5-78-M10-AS**

How to order (electropolished) **1** l<sub>1</sub>  
**2** d<sub>1</sub>  
**3** Type  
**GN 300.6-92-M12- IS**